



PANOPTIC OPHTHALMOSCOPES


EXPAND YOUR VIEW

Our **Welch Allyn PanOptic** and **PanOptic Plus** Ophthalmoscopes provides a view about 20 times that of a traditional ophthalmoscope—resulting in more complete exams in a single view¹. Enhance eye exams with the **PanOptic Plus** Ophthalmoscope, featuring **Quick Eye** alignment technology and the option to save and share eye images. Both devices work on existing Welch Allyn 3.5 V power sources.

Two indicator lights help you direct the patient's gaze for better optic disc alignment



	PanOptic Plus Ophthalmoscope	PanOptic Basic Ophthalmoscope
Model Number	118-3	118-2
iExaminer ready	Yes	No
Quick Eye Alignment Technology	Yes	No
Warranty	5 Years	1 Year
Height x Width x Depth	8 cm x 4.5 cm x 7.5 cm	
Weight	130 grams	
Apertures	Small, Large, Red Free, Slit, Fixation target, Cobalt Blue	
Diopter Range	-20 to +25 D	
Diopter Steps	-20, -15, -12, -10, -9, -8, -7, -6, -5, -4, -3, -2, -1, 0, 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 12, 15, 20, 25	
Crossed-linear Polarizers	Yes	
Lamp Type and Warranty	SureColor LED, 7 year warranty	
Color	Color rendering index (CRI): 95 typical; R9: 85 typical; Color temperature: 2700K - 3500K	
Lamp Life	80+ years ² (typical)	
Field of view	20°	



Save and share eye images with the **PanOptic Plus** device when combined with our **SmartBracket** adapter and **iExaminer Pro** App.




Standard Ophthalmoscope



PanOptic Ophthalmoscope

20X larger viewing area



	Welch Allyn Lithium Ion Plus Power Handle with USB Charger	Welch Allyn Universal Desk Charger
Model Number	719-3	719-DSK
Height x Width X Depth	14 cm x 3 cm x 3 cm	10 cm x 19 cm x 11 cm
Weight	140 grams	910 grams (not including the cord)
Compatibility	719-DSK Welch Allyn Universal Desk Charger; 71140 chargers	71140, 719-3, 71910, 71670 handles. 12800 & 22800 used with 71249 Adapter Sleeve
Integrated Charging	USB-C	—
Warranty	Two years	One year
On-time	5.5 hours; Approximately 660 30-second exams	—
Battery Type	Lithium Ion	—
USB Quick-charge time (0-75%)	90 minutes	—
Power Cord and Cord Options	719-USB	#18 AWG, 3-wire grounded cord, 6 feet long medical grade detachable with IEC60320 inlet
Input	—	100-240V, 50-60 Hz, 100mA max, Class I, Continuous Operation
Output	—	2.4V - 4.0V DC 80mA max



PANOPTIC ACCESSORIES

118-EC	Reusable Eyecup (set of five)
11840-IEX	SmartBracket phone adapter
777-LH	3.5 V Head Locking Hardware with setscrews

For more information, please contact your local Baxter Business Development Manager or Customer Care Team.

References

1. Based on Baxter Internal Testing
2. Assumes an average of 4 patient exams (both eyes) per day taking 15 seconds per eye for 200 days per year

The PanOptic is intended to be used by clinicians and medically qualified personnel for examination of the retina, cornea, aqueous, lens and vitreous of the eye under illumination and magnification on pediatric and adult patients. Medical device (2017/745/EU): Class I (CE) Manufacturer: Welch Allyn, Inc., 4341 State Street Road, Skaneateles Falls, NY 13153 USA. EC Rep.: Welch Allyn Limited, Navan Business Park, Dublin Road, Navan, County Meath, C15 AW22, Ireland. These medical devices are a regulated health product which, pursuant to such regulation bears a CE mark. Carefully read the detailed instructions for safe and proper use included in the documents accompanying the medical devices. The personnel of healthcare establishments are responsible for the proper use and maintenance of these medical devices. Baxter reserves the right to make changes without notice in design, specifications and models. The only warranty Baxter makes is the express written warranty extended on the sale or rental of its products.

Baxter.se

E hrc_ordernordic@baxter.com, T 020-78 10 30

Baxter, Hillrom, PanOptic, PanOptic Plus, Quick Eye, SmartBracket, Surecolor and Welch Allyn are trademarks of Baxter International Inc. or its subsidiaries.

Any other trademarks, product names or brand images appearing herein are the property of their respective owners.