



Key Features

- Highly conductive wet gel
- Superior adhesion
- Occlusive backing material
- Unique offset concept
- High-quality Ag/AgCl sensor

Ambu[®] Blue Sensor M

The small Ambu Blue Sensor M features highly conductive wet gel and superior adhesion to ensure optimal signal quality during short to medium-term applications. Thanks to the special occlusive backing material, the electrode will not absorb liquids.

DIMENSIONS

Electrode size (max. L x W or diameter in mm)	40.8 x 34
Skin contact size (max. L x W or diameter in mm)	34
Adhesive area (in mm ²)	754
Height excluding connector/wire (in mm)	1

SENSOR

Sensor material	Silver/silver chloride
Gel system	Wet gel
Sensor area (in mm ²)	13.2
Gel area/measuring area (in mm ²)	154

LIFETIME

Recommended application time (max.)	12 hours
In opened pouches	1 month
Unopened pouches*	15 months

*from date of production

X-RAY & MRI

X-ray-translucent	No
MRI-safe	No

ELECTRICAL DATA (ANSI/AAMI)

AC impedance - typical	400 Ω
DC offset voltage - typical	0.2 mV
Defibrillation overload recovery - typical	7.8 mV
Rate of change of polarization potential - typical	0.2 mV/s
Combined offset instability and internal noise	<15μV
Bias current tolerance (over 8 hours)	<5 mV



ENVIRONMENT

PVC-free electrode	No
Latex-free electrode	Yes
PVC-free lead wire	-
Latex-free lead wire	-
PVC-free packaging	Yes

STANDARD PACKAGING

Quantity/liner	1	
Quantity/pouch	10, 50	
Quantity/box	1000/2000	
Minimum sales	2000	

OPTIONS

Connectors	S, A, F
Pre-wired	-
Pre-wired connectors	-

AVAILABLE CONFIGURATIONS*

	Qty per inner/outer box	
M-00-S	1000/2000	1000/2000
M-00-A,F	1000/2000	

* Some configurations may not be available worldwide

 PRODUCT
 WIRE LENGTH
 CONNECTOR

M-00-S

PRECAUTION

Single patient use only


MATERIALS - ELECTRODE

Bio-compatible	Yes
Sensor	Silver/silver chloride (Ag/AgCl)
Sponge	Polyurethane foam (PUR)
Outer carrier	Polyvinyl chloride foam (PVC)
Outer adhesive	Acrylate
Inner carrier (if any)	-
Inner adhesive (if any)	-
Upper part*	Polyvinyl chloride film (PVC)
Fitting	Polypropylene (PP)
Connector (stud)	Nickel-plated brass
Lead wire core	-
Lead wire insulation	-
Lead wire connector	-
Liner	Polyester/polyethylene film (PE/PET)

MATERIALS - PACKAGING

Pouches, inner layer	Polyethylene (PE)
Pouches, centre layer	Aluminium (Al)
Pouches, outer layer	Polyester (PET)
Boxes	Cardboard

CONNECTORS



S = Stud



A = 4 mm fitting



F = 3 mm fitting

Ambu A/S

Baltorpbakken 13
 DK-2750 Ballerup
 Denmark
 T +45 72 25 20 00
 F +45 72 25 20 50
 www.ambu.com

CARDIOLOGY

