

PowerGrab™ Series

# PowerGrab™ Thermo NEW

**TOWA**  
www.towagloves.com

ULTIMATE WORKABILITY.



### DESCRIPTION

Long lasted gloves for cold weather are finally available from most trusted PowerGrab™ Series. Fully coated thumb area offers more protection. Unlike similar gloves in the market that leave the top of the thumb uncoated and unprotected, PowerGrab™ series fully coat the thumb, protecting the vulnerable area while offering an excellent grip performance.

### FEATURES

**Extra Warmth:** Napped Acrylic liner makes it possible to work under cold conditions.

**Leaching:** Proteins, chemical substances, and odor are leached from PowerGrab™ series to minimize allergic reaction.

**Safety:** Extra coating of thumb area assures the most important aspect, safety.

**Grip Performance:** Revolutionary MicroFinish™ promises outstanding wet and dry handling.

**Comfort:** A 10-gauge seamless liner and ergonomic design assure a maximum comfort and minimum hand fatigue.

### TECHNOLOGY



**MicroFinish™**

Best selling PowerGrab™ finally meets MicroFinish™ for ultimate workability.

### APPLICATIONS

Building & Construction  
Cold Condition  
Gardening  
General Purpose  
Maintenance  
Shipping & Handling

### PRODUCT

**Material** Latex  
**Size** 7/S - 11/XXL  
**Liner** 10-Gauge  
Seamless  
Napped Acrylic  
**Color** Yellow & Brown  
Orange & Brown

### STYLE / COLOR



PG Thermo/  
Orange      PG Thermo/  
Yellow

### SIZE & HEM COLOR

■ 7/S      ■ 8/M  
■ 9/L      ■ 10/XL  
■ 11/XXL


### TECHNICAL

#### EN388

Abrasion 0 **1** 2 3 4  
Cut 0 1 **2** 3 4 5  
Tear 0 1 2 **3** 4  
Puncture 0 **1** 2 3 4



### THERMOGRAPHY COMPARISON



Engineered Thermal Liner [PG Thermo]      Ordinal Liner [Similar Glove]

Tested by a public industrial testing center